

## PiX Dual Energy Box

We are excited to release the third generation of PiX Dual Energy Box. This helps to perform material discrimination using our portable imaging system. PiX DE box can be controlled directly from our Pi Gold Control Box (Rev C & above).

- DE box mounts on the X-Ray (as shown in images) with a single click.
- This model is compatible with XRS 150, 200 & 3 series with 7 pin LEMO connectors.
- DE Box compatible with constant potential generators will be launched shortly.
- It can be powered directly from the Pi Gold control box. However, it comes with a slot to place its own batteries if needed.
- The box is very light and can be rotated 360 degrees around the tube head for flexibility in the field.
- The system can be turned ON/OFF directly from the software while also allowing the flexibility to do it with a single click of the latch button.

