NDT Supply.com, Inc.

7952 Nieman Road Lenexa, KS 66214-1560 USA



W-IC Inspection Booth Purchasing Guide

•	Date:						
•	Company:						
•	Contact Name:						
•	Email Address:						
•	Phone Number:						
1)	Select Booth Model						
	☐ W-IC-1 : 40" x 30" x 34" (LxWxH), 250 lbs. (115 kg) Capacity, with: Push Handle (adds 4" to length), Rubber Work Surface, 2 Shelves and Power Bar (w/ 18' Cord and GFI)						
	☐ W-IC-2 : 60" x 30" x 34" (LxWxH), 350 lbs. (160 kg) Capacity, with: Push Handle (adds 4" to length), Rubber Work Surface, 2 Shelves and Power Bar (w/ 18' Cord and GFI)						
	☐ Custom Inspection Cart and Workpiece Fixtures, up to 96" x 60" x 34" (LxWxH)						
۵۱	Calcat Hand						
2)	Select Hood Fixed Black Nylon Hood with Frame, makes booth height 84" and operator overhang 18"						
	☐ Retractable Black Nylon Hood with Frame for heavy parts, makes height 104" when hood is folded back (Not compatible with Longitudinal Pass Through and Overhead Coil Suspension Trolly) ☐ No Hood						
3)	Do you want a Longitudinal Pass Through? If yes, specify pass-line and product diameter						
	Allows 18" of workpiece to enter the inspection area. Pass Through is fitted with brush type skirting. The pass-line and product diameter must be specified, as work surface height is adjusted accordingly.						
	☐ Yes (Requires Fixed Nylon Hood)☐ No						
4)	Select Work Surface						
	☐ Rubber Work Surface						
	☐ Coated Paper Work Surface , with paper roll and tear off edge (<i>Not compatible with Bath Recirculation System</i>)						

Phone: 913-685-0675 Fax: 913-685-1125

NDT Supply.com, Inc. 7952 Nieman Road

Lenexa, KS 66214-1560 USA



5)	Do you want t	he Bath	Recircul	ation S	System?
----	---------------	---------	----------	---------	---------

	Includes Coated Screen Work Surface (perforated to permit bath to return to tank), Hopper Style Tank (epoxy paint), Sump, Sump Drain, Pump, Agitation Nozzle and Bath Nozzle.
	 ☐ Yes (Not compatible with Coated Paper Work Surface) ☐ No
6)	Select Coil Accessories
	☐ Overhead Coil Suspension Trolley , for moving large inspection coils to the side (<i>Not compatible with Retractable Nylon Hood</i>)
	☐ Longitudinal Rails , for mounting on work surfaces. Specify additional accessories below:
	☐ Coil Cart for Longitudinal Rails, allows coil to be moved side to side
	☐ Rotatable Coil Mount for Coil Cart, allows coil to be skewed at an angle
	□ None
7)	Do you require a Coil, Yoke, Black Light or other accessories (select below)?
	☐ Coil
	☐ Yoke
	☐ Blacklight
	☐ Other (please specify): Click or tap here to enter text.
8)	Do you want to Double Workpiece Capacity?
	W-IC-1 up to 700 lbs. (320 kg) capacity, W-IC-2 up to 1100 lbs. (500 kg) capacity
	□ Yes
	□ No
9)	Do you want the Bath Starter Kit?
	Includes 1 lb. Fluorescent Powder, Centrifuge Tube, Stand for Bath Evaluation, Field Indicator (Magnetometer)
	with Helmholtz Coil +/- 10 Gauss, and Castrol Strips
	☐ Yes
	□ No

Phone: 913-685-0675 Fax: 913-685-1125

NDT Supply.com, Inc. 7952 Nieman Road

Lenexa, KS 66214-1560 USA



10)	Select	additional	accessories	desired	below:
-----	--------	------------	-------------	---------	--------

☐ White Light Fixture , with switch and option between Fixed or Retractable Hood
☐ Ventilation Fan , recommended with Bath Recirculation Systems using an oil-based carrier. Fixed or Retractable Hood options
☐ Pony Panel , brings higher voltage to the W-IC which provides 2 voltages and outlets up to the mounting panel for the Power Bar and White Light Switch. Eliminates the need for extra cords to the nspection Cart. 2 Options:
☐ 230 VAC x 60 Hz
☐ 380 (400) VAC x 50 Hz (3 Phrase)
☐ Turntable , Specify Horizontal Coil Suspension. For convenient vertical handling
\square Adjustable Height Workpiece Platform, provides a shelf to hold small parts with a weight capacity of 15 lbs. In the center of the coil
☐ Rotatable Steady Rests (2) , to allow workpiece to be placed horizontally over the work surface and rotated
□ None

Phone: 913-685-0675 Fax: 913-685-1125